

USB Classic Light / Classic Light TOP SK

Highly breathable membrane
Riwega | eternitycomfort

Construction specification
of: 01/01/2016
Art. 02010140 / 020201501
Rev.05 of: 06/07/2021

Supply and installation, including scrap, of the highly breathable membrane USB CLASSIC LIGHT, consisting of a special, high-quality cover fleece made of high-quality PP (polypropylene), water-repellent, with UV and heat stabilizer, in a medium monolithic film UV10 Bikom, highly breathable, waterproof and made of a lower moisture-absorbing polypropylene fleece.

USB CLASSIC LIGHT is installed directly on the thermo-acoustic insulation or the wooden formwork, parallel to the eaves, and fastened in the overlap zones with staples, which are covered with the next sheet. Seal the overlap zones with adhesive tape TAPE 1 PE (or the integrated double-sided adhesive tape TOP SK) to make them wind- and waterproof. All interruptions of USB CLASSIC LIGHT must be sealed with special systems according to the specific instructions provided by Riwega (see section R3 - waterproofing, air and wind tightness, and Riwega Technical Manual).

Before application, the substrate must be sufficiently free of dust and grease, clean and dry.

The fixing points of the counter battening (ventilation batten) must be sealed with the nail sealing tape TIP KONT.

Due to changing solar radiation and weather conditions, it is recommended to carry out the roofing in the prescribed time and according to the manufacturer's instructions to maintain the warranty of the sub roofing membrane by the Riwega company.

The choice of materials and processing depends on the applicable legislation.

Material	PP-composite
Film	UV10 Bikom, monolithic, elastic
Water column	> 400 cm
Mass per unit area	155 (± 5 g/m ²)
Longitudinal tear resistance	290 (± 30 N/50mm)
Transversal tear resistance	225 (± 30 N/50mm)
Sd value	0,07 m
Resistance to water passage	W1
Fire reaction class	E
UV stability	6 months
Classification UNI 11470:2015 (IT)	B

Supplier: Riwega Srl, via Isola di Sopra 28, 39044 Egna (BZ) - I

Riwega S.r.l. reserves the possibility to review or change this document. The updated document can be found on the website www.riwega.com. This document replaces the previous version.